



for bearing assembly only



SECTION P-P

		UNCHAMFERED USE ■ C0.2 □ C0.5 □ C1		SPEC : CRBC 05008 WW C1 PO L		DATE	2020.02.02
		ROUGH M/C	FIN M/C	GRD	SCALE	DWG	ChingChun
		$\sqrt{Ra 6.3}$	$\sqrt{Ra 3.2}$	$\sqrt{Ra 1.6}$	1:X	DYNAMIC RATING LOAD C (kN)	6.1
		NORMAL TOLERANCE mm				LUBRICATION	Grease
		UP TO	6	30	120	300	600
		TO	6	30	120	300	600
			±0.1	±0.2	±0.3	±0.4	±0.5
			±0.8	±1.0	±1.5	OVER 2400	
						STATIC RATING LOAD Co(kN)	8.7
						MAT	SUJ2/Equivalent
						HRC	58~64
						Note	-
						CUS IR	HIWIN
						DWG.NO.	AD007G31
DATE	MOD.	LYH		CHK			
		MODIFY		CHK			

Any and all intellectual property rights of this document are owned by HIWIN Technologies Corp. (HIWIN). You may not duplicate this document without prior authorization or approval of HIWIN. And you shall be responsible for keeping content of this document confidential. In the event of any violation of laws and/or regulations, HIWIN will seek any and all legal remedy.

HIWIN TECHNOLOGIES CORP. **CROSSED ROLLER BEARINGS**