



For bearing assembly only



UNCHAMFERED USE C0.2 C0.5 C1

SCALE 1:X

NORMAL TOLERANCE mm

UP	6	30	120	300	600	1200	2400	OVER
TO	6	30	120	300	600	1200	2400	2400
	± 0.1	± 0.2	± 0.3	± 0.4	± 0.5	± 0.8	± 1.0	± 1.5

SPEC : CRBC 07008 WW C1 PO L

DYNAMIC RATING LEAD C (mm) 7.3

STATIC RATING LEAD C (mm) 12.1

HRC 58~64 Note -

DATE 2021.02.02

DWG ChingChun

CHK Kenny

APPD LYH

CUSTR HIWIN

DWG.NO. AD007G51

2021.02.02 MOD.

MODIFY

CHK

Any and all intellectual property rights of this document are owned by HIWIN Technologies Corp. (HIWIN). You may not duplicate this document without prior authorization or approval of HIWIN. And you shall be responsible for keeping content of this document confidential. In the event of any violation of laws and/or regulations, HIWIN will seek any and all legal remedy.

HIWIN TECHNOLOGIES CORP. **CROSSED ROLLER BEARINGS**