



For bearing assembly only



2- $\phi$ 1.5 oil hole



SECTION P-P

UNCHAMFERED USE ■ C0.2 □ C0.5 □ C1

SCALE 1:X

NORMAL TOLERANCE mm

UP	5	30	120	300	600	1200	2400	OVER
TO	6	30	120	300	600	1200	2400	
	±0.1	±0.2	±0.3	±0.4	±0.5	±0.8	±1.0	±1.5

SPEC : CRBC 08008 WW C1 PO L

DYNAMIC RATING LOAD C (kN) 7.8

STATIC RATING LOAD C<sub>0</sub>(kN) 13.8

HRC 58~64 Note -

DATE 2021.02.02

DWG ChingChun

CHK Kenny

APPD LYH

CUSIR HIWIN

DWG.NO. AD007LC1

Any and all intellectual property rights of this document are owned by HIWIN Technologies Corp. (HIWIN). You may not duplicate this document without prior authorization or approval of HIWIN. And you shall be responsible for keeping content of this document confidential. In the event of any violation of laws and/or regulations, HIWIN will seek any and all legal remedy.

HIWIN TECHNOLOGIES CORP. **CROSSED ROLLER BEARINGS**