



For bearing assembly only



2- ϕ 1.5 oil hole



SECTION P-P

UNCHAMFERED USE ■ CO.2 □ CO.5 □ C1

RELIEF MC FIN MC GRD SCALE 1:X

NORMAL TOLERANCE mm

| | | | | | | | | |
|----|------|------|------|------|------|------|------|------|
| UP | 5 | 30 | 120 | 300 | 600 | 1200 | 2400 | OVER |
| TO | 6 | 30 | 120 | 300 | 600 | 1200 | 2400 | 2400 |
| | ±0.1 | ±0.2 | ±0.3 | ±0.4 | ±0.5 | ±0.8 | ±1.0 | ±1.5 |

SPEC : CRBC 09008 WW C1 PO L DATE 2021.02.02

DYNAMIC RATING LOAD C (kN) 8.3 DWG ChingChun

STATIC RATING LOAD C₀(kN) 15.5 LIBRICATION Grease CHK Kenny

HRC 58~64 Note - MAT SUJ2/Equivalent APPD LYH

CUSTR HIWIN DWG.NO. AD007LD1

Any and all intellectual property rights of this document are owned by HIWIN Technologies Corp. (HIWIN). You may not duplicate this document without prior authorization or approval of HIWIN. And you shall be responsible for keeping content of this document confidential. In the event of any violation of laws and/or regulations, HIWIN will seek any and all legal remedy.

HIWIN TECHNOLOGIES CORP. **CROSSED ROLLER BEARINGS**