



For bearing assembly only



SECTION P-P

UNCHAMFERED USE ■ C0.2 □ C0.5 □ C1

R11H MC FIN MC GRD SCALE

$\sqrt{Ra} 6.3$ $\sqrt{Ra} 3.2$ $\sqrt{Ra} 1.6$ 1: X

NORMAL TOLERANCE mm

UP	6	30	120	300	600	1200	2400	OVFR
TO	±0.1	±0.2	±0.3	±0.4	±0.5	±0.8	±1.0	±1.5

SPEC : CRBC 10008 WW C1 PO L

DATE 2021.02.02

DWG ChingChun

DYNAMIC RATING LOAD C (kN) 8.8 LUBRICATION Grease

CHK Kenny

STATIC RATING LOAD C₀(kN) 17.3 MAT SUJ2/Equivalent

APPD LYH

HRC 58~64 Note - CUSTR HIWIN

DWG.NO. ADO07LE1

Any and all intellectual property rights of this document are owned by HIWIN Technologies Corp. (HIWIN). You may not duplicate this document without prior authorization or approval of HIWIN. And you shall be responsible for keeping content of this document confidential. In the event of any violation of laws and/or regulations, HIWIN will seek any and all legal remedy.

HIWIN TECHNOLOGIES CORP. **CROSSED ROLLER BEARINGS**