



UNCHAMFERED USE		<input type="checkbox"/> CO.2	<input type="checkbox"/> CO.5	<input type="checkbox"/> C1				
ROUGH MC	FIN MC	GRD	SCALE					
6.3a	1.6a	0.4g	1: X					
∇	∇∇	∇∇∇						
NORMAL TOLERANCE mm								
UP	6	30	120	300	600	1200	2400	OVER
TO	6	30	120	300	600	1200	2400	2400
	±0.1	±0.2	±0.3	±0.4	±0.5	±0.8	±1.0	±1.5

SPEC : CRBE 16035 A WW C1 P4				DATE	2014/07/01
				DWG	Yutesn
DYNAMIC RATING LOAD C <sub>1000</sub>	102	LUBRICATION	Grease	CHK	Regan
STATIC RATING LOAD C <sub>01000</sub>	192.3	MAT	SUJ2/Equivalent	APPD	Fachih
HRC	58~64	CUSTR	HIWIN		
			DWG.NO.	AD050221	

機密級 More Confidential

HIWIN TECHNOLOGIES CROSSED ROLLER BEARINGS

DATE	MODIFY	CHK
------	--------	-----