



SECTION A-A

UNCHAMFERED USE		<input type="checkbox"/> C0.2	<input type="checkbox"/> C0.5	<input type="checkbox"/> C1	SCALE		SPEC : CRBE 05515 A WW C1 P4		DATE	2014/05/31			
ROUGH MC	FIN MC	GRD	<input type="checkbox"/> 0.4g <input type="checkbox"/> 0.2g <input type="checkbox"/> 0.1g		1: X		DYNAMIC RATING LOAD C ₁₀₀₀		21.7	LUBRICATION	Grease	DWG	Fachih
6.3 σ	1.6 σ	0.4g					STATIC RATING LOAD C ₀₄₀₀		30.6	MAT	SUJ2/Equivalent	CHK	John
NORMAL TOLERANCE mm													
UP	6	30	120	300	600	1200	2400	2400	HRC		58~64	CUSTR	HIWIN
TO	±0.1	±0.2	±0.3	±0.4	±0.5	±0.8	±1.0	±1.5				DWG.NO.	AD200181
HIWIN TECHNOLOGIES CROSSED ROLLER BEARINGS													

機密級 More Confidential

DATE	MODIFY	CHK
------	--------	-----