



For bearing assembly only



SECTION P-P

UNCHAMFERED USE		■ CO.2 □ CO.5 □ C1	
ROUGH MC	FIN MC	GRD	SCALE
$\sqrt{Ra 6.3}$	$\sqrt{Ra 3.2}$	$\sqrt{Ra 1.6}$	1:X
NORMAL TOLERANCE mm			
UP TO	6	30	120
TO	6	30	120
	30	120	300
	300	600	1200
	600	1200	2400
	1200	2400	OVER
	±0.1	±0.2	±0.3
	±0.4	±0.5	±0.8
	±1.0	±1.5	

SPEC : CRBE 08022 A WW C1 P4		DATE	2020.07.09
DYNAMIC RATING LOAD C (kN)		40.4	LUBRICATION
STATIC RATING LOAD C <sub>0</sub> (kN)		63.6	Grease
HRC		58~64	CHK
Note		-	CBJ
CUS:R		HIWIN	
DWC:NO.		AD201AA1	

機密級 More Confidential

HIWIN TECHNOLOGIES CORP. **CROSSED ROLLER BEARINGS**