



UNCHAMFERED USE ■ CO.2 □ CO.5 □ C1

ROUGH FIN GRD SCALE

√Ra 6.3 √Ra 3.2 √Ra 1.6

NORMAL TOLERANCE mm

UP	6	30	120	300	600	1200	2400	OVLR
TO	±0.1	±0.2	±0.3	±0.4	±0.5	±0.8	±1.0	±1.5

SPEC : CRBE 11528 A NN C1 P4

DYNAMIC RATING LOAD C $\phi 40$ 73.1 LUBRICATION Grease

STATIC RATING LOAD C $\phi 40$ 131.9 MAT SUJ2/Equivalent

HRC 58~64 Note - CUSTR HIWIN

DATE 2021.02.02

DWG ChingChun

CHK Kenny

APPD LYH

HIWIN TECHNOLOGIES CORP. **CROSSED ROLLER BEARINGS** DWG.NO. AD201C01

Any and all intellectual property rights of this document are owned by HIWIN Technologies Corp. (HIWIN). You may not duplicate this document without prior authorization or approval of HIWIN. And you shall be responsible for keeping content of this document confidential. In the event of any violation of laws and/or regulations, HIWIN will seek any and all legal remedy.