



1 A11YOZA1

2 Released by HIWIN design group.

3 列印者:00020334 黃品絲 印刷時間:2021/06/08 19:13:41

4 (C) (C) (C)

機密級 More Confidential



PRELOAD(kgf)	~
R.D.	~
S.F. (kgf)	~
DRAG TORQUE(kgf-cm)	~
DIRECTION OF TURN	R
P.C. DIA.	15.96
BALL DIA.	3.175
BACKLASH	0.04MAX
CIRCUIT	3
LEAD ANGLE	11.28
DYNAMIC (kgf)	900
STATIC (kgf)	1860
LEAD	10

SPEC: R16-10K3-FSC

MAX. AXIAL LOAD(kgf)		LUBRICATION		BALL DIA.	3.175
MAX. ROTATIONAL SPEED (rpm)		SPACE BALL		BACKLASH	0.04MAX
DN VALUE		E1 TYPE ASSEMBLY METHOD		CIRCUIT	3
MAX. FEED RATE(m/min)		CUSTOMER DRAWING NO.		LEAD ANGLE	11.28
ACCELERATION (m/sec ²)		CUSTOMER MC TYPE		DYNAMIC (kgf)	900
SUPPORT METHOD		CUSTOMER AXIAL TYPE		STATIC (kgf)	1860
				LEAD	10

	UNCHAMFERED USE <input checked="" type="checkbox"/> C0.5 <input type="checkbox"/> C1 <input type="checkbox"/> C ROUGH M/C/FIN M/C GRD 25g 6.3g 0.4g SCALE 1: X	MAT. SH:ROLLED DATE 2011.05.24
	NORMAL TOLERANCE mm UP TO 6 30 120 300 600 1200 2400 OVER 2400 ±0.1 ±0.2 ±0.3 ±0.4 ±0.5 ±0.8 ±1.0 ±1.5	NT:SNCM220/Equivalent DWG Kelly THREAD BALL TRACK CHK Sting HRC 56 ~ 62 APPD Jamin
CUSTR HIWIN STD.		DWG.NO. A11YOZA1

*BREAK SHARP EDGE UNLESS OTHER SPECIFIED.
*未畫倒角者去毛邊 (C0.2MAX)
● THREAD END ALLOWS ABOVE LENGTH OUT OF HARDNESS TOLERANCE

機密級 More Confidential

* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.

DATE	MODIFICATION	APPROVED
------	--------------	----------