



PRELOAD(kgf)	~
R.D.	~
S.F. (kgf)	~
DRAG TORQUE(kgf-cm)	~
DIRECTION OF TURN	R
P.C. DIA.	15.675

SPEC: 4R15-20K4-DFSC

MAX. AXIAL LOAD(kgf)	LUBRICATION	BALL DIA.	3.175
MAX. ROTATIONAL SPEED (rpm)	SPACE BALL	BACKLASH	0.04MAX
DN VALUE	E1 TYPE ASSEMBLY METHOD	CIRCUIT	4
MAX. FEED RATE(m/min)	CUSTOMER DRAWING NO.	LEAD ANGLE	22.1
ACCELERATION(m/sec ²)	CUSTOMER MC TYPE	DYNAMIC (kgf)	1040
SUPPORT METHOD	CUSTOMER AXIAL TYPE	STATIC (kgf)	2260
		LEAD/PITCH	20/10

UNCHAMFERED USE	<input checked="" type="checkbox"/> C0.5	<input type="checkbox"/> C1	<input type="checkbox"/> C	MAT.	SH-ROLLED	DATE	2019.12.17
ROUGH M/C	FIN M/C	GRD	SCALE	INT:	SNCM220/Equivalent	DWG	Melanie
√Ra25	√Ra6.3	√Ra0.4	1: X	THREAD BALL TRACK	HRC 56 ~ 62	CHK	Sting
NORMAL TOLERANCE mm				CUSTR	HIWIN STD.		
UP	6	30	120	300	600	1200	2400
TO	±0.1	±0.2	±0.3	±0.4	±0.5	±0.8	±1.0
OVER							±1.5
HIWIN BALLSCREWS				DWG.NO.	A13TV3A1		

* BREAK SHARP EDGE UNLESS OTHER SPECIFIED.
* 未量倒角者去毛邊 (CO.2MAX)
* THREAD END ALLOWS ABOVE LENGTH OUT OF HARDNESS TOLERANCE.

機密級 More Confidential