



| | | |
|------------|---------------------------|----------|
| 2021.04.30 | MOD. $\Delta \sim \Delta$ | Sting |
| DATE | MODIFICATION | APPROVED |

* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.

| | | | |
|------------------------------------|-------------------------|---------------------|--|
| SPEC: 2R12-10K3-FSC-1000-1000-0.05 | | PRELOAD(kgf) | ~ |
| MAX. AXIAL LOAD(kgf) | LUBRICATION | R.D. | 9.622 |
| MAX. ROTATIONAL SPEED (rpm) | SPACE BALL | S.F. (kgf) | ~ |
| DN VALUE | E1 TYPE ASSEMBLY METHOD | DRAG TORQUE(kgf-cm) | ~ |
| MAX. FEED RATE (m/min) | CUSTOMER DRAWING NO. | DIRECTION OF TURN | R |
| ACCELERATION (m/sec ²) | CUSTOMER MC TYPE | P.C. DIA. | 12.08 |
| SUPPORT METHOD | CUSTOMER AXIAL TYPE | BALL DIA. | 2.381 |
| | | BACKLASH | 0.02MAX |
| | | CIRCUIT | 3 |
| | | LEAD ANGLE | 14.76 |
| | | DYNAMIC (kgf) | 520 |
| | | STATIC (kgf) | 1030 |
| | | LEAD/PITCH | 10/5 |
| | | MAT. | SH:CF53/Equivalent NT:SNM220/Equivalent |
| | | DATE | 2021.04.30 |
| | | DWG | Hani |
| | | THREAD BALL TRACK | CHK Shower |
| | | HRC 56 ~ 62 | APPD Sting |
| | | CUSTR | H-CHICAGO |
| | | DWG.NO. | A141LXA2 |