

1 2 3 4 5 6 7 8 9


A
B
C
D
E
F
G



*BREAK SHARP EDGE UNLESS OTHER SPECIFIED
*未畫倒角者去毛邊

PRELOAD (kgf)	_____
R.D	45.44
S.F (kgf)	_____
DRAG TORQUE(kgf-cm)	_____
LUBRICATION	_____
DIRECTION OF TURN	RIGHT
PC DIA	51.93
BALL DIA	6.35
BALL TRACK FORM	GOTHIC
BACKLASH	_____
CIRCUIT	_____
LEAD ANGLE	3.51°
DYNAMIC (kgf)	_____
STATIC (kgf)	_____
LEAD	10.

SPEC: R50-10-5600-5600-0.05



CUSTOMER DRAWING NO.	_____
MC TYPE	_____
ANAL TYPE	_____

UNCHAMFERED USE	<input type="checkbox"/> C0.5	<input type="checkbox"/> C1	<input type="checkbox"/> C
ROUGH M/C FIN M/C	6.3	0.4	0.05
UNTOL	UNTOL	UNTOL	UNTOL
DIMAN	mm	mm	mm
UP	6	30	120
TO	6	30	120
±0.1	±C2	±0.3	±0.4
±0.5	±0.8	±1.0	±1.5
THREAD BALL TRACK	HRC 56 ~ 62		

CUSTR	HIWIN STD	DATE	07.08.98
SCALE	1: X	DWG	盧文雄
TITLE	BALL SCREW	CHK	_____
MATAL	CF53	APPD	_____
DWG.NO.	A109NKA1	PROCESS NO	E

DATE	MODIFICATION	APPROVED

* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.

HIWIN® BALLSCREWS