




機密級 More Confidential



PRELOAD(kgf)	~
R.D.	~
S.F. (kgf)	~
DRAG TORQUE(kgf-cm)	~
DIRECTION OF TURN	R
P.C. DIA.	51.93
BALL DIA.	6.35
BACKLASH	0.07MAX
CIRCUIT	6
LEAD ANGLE	3.51
DYNAMIC (kgf)	7450
STATIC (kgf)	25350
LEAD	10

SPEC:R50-10K6-FSC

MAX. AXIAL LOAD(kgf)		LUBRICATION		BALL DIA.	6.35
MAX. ROTATIONAL SPEED (rpm)		SPACE BALL		BACKLASH	0.07MAX
DN VALUE		EI TYPE ASSEMBLY METHOD		CIRCUIT	6
MAX. FEED RATE(m/min)		CUSTOMER DRAWING NO.		LEAD ANGLE	3.51
ACCELERATION (m/sec ²)		CUSTOMER MC TYPE		DYNAMIC (kgf)	7450
SUPPORT METHOD		CUSTOMER AXIAL TYPE		STATIC (kgf)	25350
				LEAD	10



UNCHAMFERED USE	<input type="checkbox"/> C0.5	<input checked="" type="checkbox"/> C1	<input type="checkbox"/> C
ROUGH M/C/FIN M/C	GRD	<input type="checkbox"/> 0.4g	<input type="checkbox"/> 0.4g
SCALE	1: X		
NORMAL TOLERANCE mm			
UP TO 6	6-30	30-120	120-300
±0.1	±0.2	±0.3	±0.4
300-600	600-1200	1200-2400	OVER 2400
±0.4	±0.5	±0.8	±1.0
			±1.5

MAT.	SH:ROLLED	DATE	2012.06.20
	NT:SNCM220/Equivalent	DWG	Jamin
THREAD BALL TRACK	CHK	Michelle	
HRC 56 ~ 62	APPD	Cody	
CUSTR	HIWIN STD.		
DWG.NO.	A126E2A1		

*BREAK SHARP EDGE UNLESS OTHER SPECIFIED.
 *未畫倒角者去毛邊 (C0.2MAX)
 *THREAD END ALLOWS ABOVE LENGTH OUT OF HARDNESS TOLERANCE

機密級 More Confidential

* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.

DATE	MODIFICATION	APPROVED