


機密級 More Confidential

A
B
C
D
E
F
G



PRELOAD(kgf)	~
R.D	12.399
S.F (kgf)	~
DRAG TORQUE(kgf-cm)	~
DIRECTION OF TURN	R
PC DIA.	15.675

SPEC: 4R15-20-3000-3000-0.05

MAX. AXIAL LOAD(kgf)		LUBRCATION		BALL DIA.	3.175
MAX. ROTATIONAL SPEED (rpm)		SPACE BALL		BACKLASH	~
DN VALUE		EI TYPE ASSEMBLY METHOD		CIRCUIT	~
MAX. FEED RATE(m/min)		CUSTOMER DRAWING NO.		LEAD ANGLE	22.1
ACCELERATION (m/sec ²)		CUSTOMER MC TYPE		DYNAMIC (kgf)	~
SUPPORT METHOD		CUSTOMER AXIAL TYPE		STATIC (kgf)	~
				LEAD /PITCH	20/5

<p>THREAD LENGTH E300: 0.05</p>	UNCHAMFERED USE <input type="checkbox"/> R0.5 <input checked="" type="checkbox"/> R1 <input type="checkbox"/> R ROUGH M/C/FIN M/C GRD <input type="checkbox"/> SCALE 1: X 25 μ 6.3 μ 0.4 μ	MATAL SH: CF53	DATE 2006.12.29
	UNTOL DIMN mm UP 6 30 120 300 600 1200 2400 OVER TO ± 0.1 ± 0.2 ± 0.3 ± 0.4 ± 0.5 ± 0.8 ± 1.0 ± 1.5	THREAD BALL TRACK APPD SIGMA HRC 56 ~ 62	CUSTR HIWIN DWG.NO. A110WKA1

*BREAK SHARP EDGE UNLESS OTHER SPECIFIED.
 *未量倒角者以R0.5MAX
 * THREAD END ALLOWS ABOVE LENGTH OUT OF HARDNESS TOLERANCE

機密級 More Confidential

* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.

DATE	MODIFICATION	APPROVED