



A141MAA2

More Confidential

$\sqrt{Ra6.3}$ ($\sqrt{Ra0.4}$)



PRELOAD(kgf)	~
R.D.	7.742
S.F. (kgf)	~
DRAG TORQUE(kgf-cm)	~
DIRECTION OF TURN	R
P.C. DIA.	10.2
BALL DIA.	2.381
BACKLASH	0.02MAX
CIRCUIT	2.6*1
LEAD ANGLE	7.12
DYNAMIC (kgf)	450
STATIC (kgf)	790
LEAD	4

△ △
SPEC: R10-4B1-FSZ-700-700-0.05

MAX. AXIAL LOAD (kgf)		LUBRICATION		BALL DIA.	2.381
MAX. ROTATIONAL SPEED (rpm)		SPACE BALL		BACKLASH	0.02MAX
DN VALUE		E1 TYPE ASSEMBLY METHOD		CIRCUIT	2.6*1
MAX. FEED RATE (m/min)		CUSTOMER DRAWING NO.		LEAD ANGLE	7.12
ACCELERATION (m/sec ²)		CUSTOMER MC TYPE		DYNAMIC (kgf)	450
SUPPORT METHOD		CUSTOMER AXIAL TYPE		STATIC (kgf)	790
				LEAD	4

	UNCHAMFERED USE <input checked="" type="checkbox"/> C0.5 <input type="checkbox"/> C1 <input type="checkbox"/> C	SCALE	MAT.	SH:CF53/Equivalent	DATE	2021.05.03
	ROUGH M/C/FIN M/C/GRD <input type="checkbox"/> <input type="checkbox"/> <input type="checkbox"/>	SCALE	1: X	INT:SNM220/Equivalent	DWG	Hani
$\sqrt{Ra25}$ $\sqrt{Ra6.3}$ $\sqrt{Ra0.4}$	NORMAL TOLERANCE mm		THREAD BALL TRACK	CHK	Shower	
UP TO 6 30 120 300 600 1200 2400 OVER	±0.1 ±0.2 ±0.3 ±0.4 ±0.5 ±0.8 ±1.0 ±1.5		HRC 56 ~ 62	APPD	Sting	
$r/300p: 0.05$ $ep: \triangle 0.117$			CUSTR	H-CHICAGO		
*BREAK SHARP EDGE UNLESS OTHER SPECIFIED. *未量倒角者去毛邊 (CO.2MAX) * THREAD END ALLOWS ABOVE LENGTH OUT OF HARDNESS TOLERANCE		DWG.NO.		A141MAA2		

2021.05.03	MOD. △ ~ △	Sting
DATE	MODIFICATION	APPROVED

* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.