



A141MEA2

More Confidential

$\sqrt{Ra6.3}$ ($\sqrt{Ra0.4}$)



PRELOAD(kgf)	~
R.D.	6.418
S.F. (kgf)	~
DRAG TORQUE(kgf-cm)	~
DIRECTION OF TURN	R
P.C. DIA.	7.98
BALL DIA.	1.5
BACKLASH	0.01MAX
CIRCUIT	3.6*1
LEAD ANGLE	4.56
DYNAMIC (kgf)	290
STATIC (kgf)	540
LEAD	2

SPEC: R8-2C1-FSZ-500-500-0.05

MAX. AXIAL LOAD (kgf)		LUBRICATION		BALL DIA.	1.5
MAX. ROTATIONAL SPEED (rpm)		SPACE BALL		BACKLASH	0.01MAX
DN VALUE		E1 TYPE ASSEMBLY METHOD		CIRCUIT	3.6*1
MAX. FEED RATE (m/min)		CUSTOMER DRAWING NO.		LEAD ANGLE	4.56
ACCELERATION (m/sec ²)		CUSTOMER MC TYPE		DYNAMIC (kgf)	290
SUPPORT METHOD		CUSTOMER AXIAL TYPE		STATIC (kgf)	540
				LEAD	2

	UNCHAMFERED USE	<input checked="" type="checkbox"/> C0.5	<input type="checkbox"/> C1	<input type="checkbox"/> C	MAT. SH:CF53/Equivalent INT:SNCM220/Equivalent DATE 2021.04.30
	ROUGH M/C/FIN M/C/I	GRD	SCALE 1: X		
*BREAK SHARP EDGE UNLESS OTHER SPECIFIED. *未量倒角者去毛邊 (CO.2MAX) * THREAD END ALLOWS ABOVE LENGTH OUT OF HARDNESS TOLERANCE.	NORMAL TOLERANCE mm UP TO 6 30 120 300 600 1200 2400 OVER ±0.1 ±0.2 ±0.3 ±0.4 ±0.5 ±0.8 ±1.0 ±1.5		CUSTR H-CHICAGO DWG.NO. A141MEA2		
1/300p: 0.05 ep: 0.083	HIWIN BALLSCREWS				

2021.04.30	MOD.		Michelle
DATE	MODIFICATION	APPROVED	

* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.