



A141MMA2 More Confidential


$\sqrt{Ra6.3}$ ($\sqrt{Ra0.4}$)



PRELOAD(kgf)	~
R.D.	5.228
S.F. (kgf)	~
DRAG TORQUE(kgf-cm)	~
DIRECTION OF TURN	R
P.C. DIA.	6.79
BALL DIA.	1.5
BACKLASH	0.01MAX
CIRCUIT	2.6*1
LEAD ANGLE	5.36
DYNAMIC (kgf)	200
STATIC (kgf)	340
LEAD	2

SPEC: R6-2B1-FSZ-500-500-0.05

MAX. AXIAL LOAD (kgf)		LUBRICATION		BALL DIA.	1.5
MAX. ROTATIONAL SPEED (rpm)		SPACE BALL		BACKLASH	0.01MAX
DN VALUE		E1 TYPE ASSEMBLY METHOD		CIRCUIT	2.6*1
MAX. FEED RATE (m/min)		CUSTOMER DRAWING NO.		LEAD ANGLE	5.36
ACCELERATION (m/sec ²)		CUSTOMER MC TYPE		DYNAMIC (kgf)	200
SUPPORT METHOD		CUSTOMER AXIAL TYPE		STATIC (kgf)	340
				LEAD	2



*BREAK SHARP EDGE UNLESS OTHER SPECIFIED.
*未量倒角者去毛邊 (CO.2MAX)
* THREAD END ALLOWS ABOVE LENGTH OUT OF HARDNESS TOLERANCE.

UNCHAMFERED USE	<input checked="" type="checkbox"/> C0.5	<input type="checkbox"/> C1	<input type="checkbox"/> C
ROUGH M/C/FIN M/C/I	<input checked="" type="checkbox"/> GRD	<input type="checkbox"/>	<input type="checkbox"/>
SCALE	1: X		
MAT.	SH:CF53/Equivalent	DATE	2021.04.30
	INT:SNM220/Equivalent	DWG	Melanie
THREAD BALL TRACK	CHK	Michelle	
HRC 56 ~ 62	APPD	Michelle	
CUSTR	H-CHICAGO		
DWG.NO.	A141MMA2		

2021.04.30	MOD.		Michelle
DATE	MODIFICATION	APPROVED	

* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.

HIWIN BALLSCREWS