



A142D0A1

More Confidential

$\sqrt{Ra6.3}$  ( $\sqrt{Ra0.4}$ )



PRELOAD(kgf)	~
R.D.	~
S.F. (kgf)	~
DRAG TORQUE(kgf-cm)	~
DIRECTION OF TURN	R
P.C. DIA.	16.175
BALL DIA.	3.175
BACKLASH	0.03MAX
CIRCUIT	2.6*1
LEAD ANGLE	5.62
DYNAMIC (kgf)	860
STATIC (kgf)	1760
LEAD	5

SPEC: R16-5B1-FSZ

MAX. AXIAL LOAD (kgf)		LUBRICATION	BALL DIA.	3.175
MAX. ROTATIONAL SPEED (rpm)		SPACE BALL	BACKLASH	0.03MAX
DN VALUE		E1 TYPE ASSEMBLY METHOD	CIRCUIT	2.6*1
MAX. FEED RATE (m/min)		CUSTOMER DRAWING NO.	LEAD ANGLE	5.62
ACCELERATION (m/sec <sup>2</sup> )		CUSTOMER MC TYPE	DYNAMIC (kgf)	860
SUPPORT METHOD		CUSTOMER AXIAL TYPE	STATIC (kgf)	1760
			LEAD	5

	UNCHAMFERED USE <input checked="" type="checkbox"/> C0.5 <input type="checkbox"/> C1 <input type="checkbox"/> C ROUGH M/C FIN M/C GRD <input type="checkbox"/> SCALE 1: X $\sqrt{Ra25}$ $\sqrt{Ra6.3}$ $\sqrt{Ra0.4}$	MAT. SH: ROLLED DATE 2021.06.09 INT: SNCM220/Equivalent DWG Melanie THREAD BALL TRACK CHK Shower HRC 56 ~ 62 APPD Michelle
	NORMAL TOLERANCE mm UP TO 6 30 120 300 600 1200 2400 OVER ±0.1 ±0.2 ±0.3 ±0.4 ±0.5 ±0.8 ±1.0 ±1.5 CUSTR <b>H-CHICAGO</b> DWG.NO. <b>A142D0A1</b>	*BREAK SHARP EDGE UNLESS OTHER SPECIFIED. *未量倒角者去毛邊 (CO.2MAX) ● THREAD END ALLOWS ABOVE LENGTH OUT OF HARDNESS TOLERANCE.

DATE	MODIFICATION	APPROVED
------	--------------	----------

\* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.