

A141MHA2

More Confidential

$\sqrt{Ra6.3}$  ( $\sqrt{Ra0.4}$ )

A  
B  
C  
D  
E  
F  
G

$\Delta$  500

$\Delta$  37

5

10

2

5

D

D

( $\phi$ 8)


$\Delta$

WIPER THIS END  
(單邊附刮刷器)

M22x1P  
MD22 $_{-0.206}^{+0.026}$   
PD21.35 $_{-0.144}^{+0.026}$

$\phi$ 20

$\phi$ 24 $_{-0.1}^0$



D-D VIEW


SPEC: R8-5B1-RST-500-500-0.05

MAX. AXIAL LOAD (kgf)	LUBRICATION	BALL DIA.	2
MAX. ROTATIONAL SPEED (rpm)	SPACE BALL	BACKLASH	0.02MAX
DN VALUE	E1 TYPE ASSEMBLY METHOD	CIRCUIT	2.6*1
MAX. FEED RATE (m/min)	CUSTOMER DRAWING NO.	LEAD ANGLE	10.96
ACCELERATION (m/sec <sup>2</sup> )	CUSTOMER MC TYPE	DYNAMIC (kgf)	320
SUPPORT METHOD	CUSTOMER AXIAL TYPE	STATIC (kgf)	540
		LEAD	5

PRELOAD (kgf)	~
R.D.	6.156
S.F. (kgf)	~
DRAG TORQUE (kgf-cm)	~
DIRECTION OF TURN	R
P.C. DIA.	8.22

UNCHAMFERED USE	<input checked="" type="checkbox"/> C0.5	<input type="checkbox"/> C1	<input type="checkbox"/> C	MAT.	SH:CF53/Equivalent	DATE	2021.04.30	
ROUGH M/C/FIN M/C/GRD	<input type="checkbox"/> $\sqrt{Ra25}$	<input type="checkbox"/> $\sqrt{Ra6.3}$	<input type="checkbox"/> $\sqrt{Ra0.4}$	SCALE	INT:SNCM220/Equivalent	DWG	Melanie	
	NORMAL TOLERANCE mm			1: X	THREAD BALL TRACK	CHK	Michelle	
	UP TO	6	30	120	300	600	1200	2400
		$\pm 0.1$	$\pm 0.2$	$\pm 0.3$	$\pm 0.4$	$\pm 0.5$	$\pm 0.8$	$\pm 1.0$
		$\pm 0.1$	$\pm 0.2$	$\pm 0.3$	$\pm 0.4$	$\pm 0.5$	$\pm 0.8$	$\pm 1.5$
		HITWIN BALLSCREWS			CUSTR	H-CHICAGO		
		DWG.NO.			A141MHA2			

\*BREAK SHARP EDGE UNLESS OTHER SPECIFIED.  
\*未量倒角者去毛邊 (CO.2MAX)  
THREAD END ALLOWS ABOVE LENGTH OUT OF HARDNESS TOLERANCE.



2021.04.30	MOD.	$\Delta$ ~ $\Delta$	Michelle
DATE	MODIFICATION	APPROVED	

\* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.