



A142P2A2

More Confidential


$\sqrt{Ra6.3}$  ( $\sqrt{Ra0.4}$ )



PRELOAD(kgf)	~
R.D.	~
S.F. (kgf)	~
DRAG TORQUE(kgf-cm)	~
DIRECTION OF TURN	R
P.C. DIA.	41.85
BALL DIA.	6.35
BACKLASH	$\Delta$ 0.07MAX
CIRCUIT	4
LEAD ANGLE	4.35
DYNAMIC (kgf)	4660
STATIC (kgf)	13120
LEAD	10

SPEC: R40-10K4-FSC

MAX. AXIAL LOAD (kgf)	LUBRICATION	BALL DIA.	6.35	
MAX. ROTATIONAL SPEED (rpm)	SPACE BALL	BACKLASH	$\Delta$ 0.07MAX	
DN VALUE	E1 TYPE ASSEMBLY METHOD	CIRCUIT	4	
MAX. FEED RATE (m/min)	CUSTOMER DRAWING NO.	LEAD ANGLE	4.35	
ACCELERATION (m/sec <sup>2</sup> )	CUSTOMER MC TYPE	DYNAMIC (kgf)	4660	
SUPPORT METHOD	CUSTOMER AXIAL TYPE	STATIC (kgf)	13120	
	端塞型式	不出牙	LEAD	10



UNCHAMFERED USE	<input type="checkbox"/> C0.5	<input checked="" type="checkbox"/> C1	<input type="checkbox"/> C					
ROUGH M/C	FIN M/C	GRD	SCALE					
$\sqrt{Ra25}$	$\sqrt{Ra6.3}$	$\sqrt{Ra0.4}$	1: X					
NORMAL TOLERANCE mm								
UP TO	6	30	120	300	600	1200	2400	OVER 2400
	$\pm 0.1$	$\pm 0.2$	$\pm 0.3$	$\pm 0.4$	$\pm 0.5$	$\pm 0.8$	$\pm 1.0$	$\pm 1.5$

MAT.	SH: ROLLED	DATE	2021.07.20
	INT: SNCM220/Equivalent	DWG	Hanna
THREAD BALL TRACK	CHK	Michelle	
HRC	56 ~ 62	APPD	Michelle
CUSTR	H-CHICAGO		
DWG.NO.	A142P2A2		

\*BREAK SHARP EDGE UNLESS OTHER SPECIFIED.  
\*未量倒角者去毛邊 (CO.2MAX)

THREAD END ALLOWS ABOVE LENGTH OUT OF HARDNESS TOLERANCE

HIWIN BALLSCREWS

2021.07.20	MOD.	$\Delta$	Michelle
DATE	MODIFICATION	APPROVED	

\* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.