


1 2 3 4 5 6 7 8 9

A
B
C
D
E
F
G



*BREAK SHARP EDGE UNLESS OTHER SPECIFIED
*未畫倒角者去毛刺

PRELOAD (kgf)	_____
R. D	15,982
S. F (kgf)	_____
DRAG TORQUE (kgf-cm)	_____
LUBRICATION	_____
DIRECTION OF TURN	RIGHT
PC DIA.	20.85
BALL DIA.	4.763
BALL TRACK FORM	GOTHIC
BACKLASH	_____
CIRCUIT	_____
LEAD ANGLE	8.6°
DYNAMIC (kgf)	_____
STATIC (kgf)	_____
LEAD	10

SPEC: R20-10-3000-3000-0.05



CUSTOMER DRAWING NO.	_____
INC. TYPE	_____
ANAL. TYPE	_____



E300: 0.05

UNCHARACTERED USE	<input type="checkbox"/> C0.5	<input type="checkbox"/> C1	<input type="checkbox"/> C3
ROUGHNESS	6.3	3.2	1.6
GRD	0.4	0.2	0.1
SCALE	1: X		
CUSTOMER	HIWIN STD.	DATE	07.08.'98
TITLE	BALL SCREW	DWG	顏興光
MATERIAL	CF53	APPD	_____
DRAWING NO.	A109N9A1	PROCESS NO.	E
THREAD BALL TRACK	HRc 56 ~ 62	THREAD END ALLOWING ABOVE LENGTH OUT OF HARDNESS TOLERANCE	

CUSTOMER	HIWIN STD.	DATE	07.08.'98
TITLE	BALL SCREW	DWG	顏興光
MATERIAL	CF53	APPD	_____
DRAWING NO.	A109N9A1	PROCESS NO.	E
THREAD BALL TRACK	HRc 56 ~ 62	THREAD END ALLOWING ABOVE LENGTH OUT OF HARDNESS TOLERANCE	

HIWIN BALLSCREWS

* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.

DATE	MODIFICATION	APPROVED