



More Confidential

▽ (▽▽)



NOTE: SPRING FORCE IS DEFINED BY WIPER BCD 36.  
(彈簧力由刮刷器固定孔拉測 BCD36.)



D-D VIEW

PRELOAD(kgf)	47
R.D.	16.924
S.F. (kgf)	0.08~0.67
DRAG TORQUE(N-m)	0.13~1.21
DIRECTION OF TURN	R
P.C. DIA.	20.2
BALL DIA.	3.175
BACKLASH	0
CIRCUIT	4
LEAD ANGLE	4.51
DYNAMIC (kgf)	938
STATIC (kgf)	1993
LEAD	5

SPEC: R20-5T4-RSI-600-600-0.023

MAX. AXIAL LOAD(kgf)	LUBRICATION	
MIN. ROTATIONAL SPEED (rpm)	SPACE BALL	
DN VALUE	B TYPE ASSEMBLY METHOD	
MAX. FEED RATE (m/min)	CUSTOMER DRAWING NO.	
ACCELERATION (m/sec <sup>2</sup> )	CUSTOMER MC TYPE	
SUPPORT METHOD	CUSTOMER AXIAL TYPE	

UNCAMFERED USE	<input checked="" type="checkbox"/> CO.5 <input type="checkbox"/> C1 <input type="checkbox"/> C	SH: OF53/Equivalent	DATE	2015.12.17	
ROUGH MARGIN W/C	GRD	NT: SNCM220/Equivalent	DWG	Shower	
SCALE	1: X	THREAD BALL TRACK	CHK	Ella	
NORMAL TOLERANCE mm		HRC	56 ~ 62	APPD	Nick

UP	16	30	120	300	600	1200	2400	2400
TO	6	30	120	300	600	1200	2400	2400
±	±0.1	±0.2	±0.3	±0.4	±0.5	±0.8	±1.0	±1.5

DATE MODIFICATION APPROVED \* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.

\*BREAM SHARP EDGE UNLESS OTHER SPECIFIED  
\*未書明時請去毛邊 (CO.2MAX)  
● THREAD END ALLOWS ABOVE LENGTH  
OUT OF HARDNESS TOLERANCE

HIWIN BALLSCREWS

DWG. NO. C-HIW-17-89