

1 2 3 4 5 6 7 8 9

A

B


C

D

E

F

G




*BREAK SHARP EDGE UNLESS OTHER SPECIFIED

*未量例角者去毛邊

PRELOAD(kgf)	_____
R. D	35.36
S. F (kgf)	_____
DRAG TORQUE(Ng-cm)	_____
LUBRICATION	_____
DIRECTION OF TURN	RIGHT
PC DIA.	41.85
BALL DIA.	6.35
BALL TRACK FORM	GOTHIC
BACKLASH	_____
CIRCUIT	_____
LEAD ANGLE	4.35°
DYNAMIC (kgf)	_____
STATIC (kgf)	_____
LEAD	10.

SPEC: R40-10-5600-5600-0.05



UNCHAMFERED USE <input type="checkbox"/> CO.5 <input checked="" type="checkbox"/> C1 <input type="checkbox"/> C	SCALE	CUSTR	HIWIN STD.	DATE
ROUGH M/C FIN M/C I GPC 0.4g 0.4g 0.4g	1: X		BALL SCREW	DWG 盧文雄
UNTOL DIMN mm		MATAL	CF53	CHK
UP TO 6 30 120 300 500 600 1200 2400 2400		DWG.NO.	A109NHAI	APPD
±0.1 ±0.2 ±0.3 ±0.4 ±0.5 ±0.8 ±1.0 ±1.5		THREAD BALL TRACK		PROCESS NO. E
HRC 56 ~ 62		THREAD END ALLOWS ABOVE LENGTH OUT OF HARDNESS TOLERANCE	HIWIN® BALLSCREWS	

DATE	MODIFICATION	APPROVED

* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.