


1 A10SL9A1

2 Released by HIWIN design group.

3  
4  
5  
6  
7  
8  
9  
G (G)

A  
B  
C  
D  
E  
F  
G




NOTE: 搭配 A10SKU 螺帽出貨

SPEC: 4R20-20-3000-3000-0.05

MAX. AXIAL LOAD(kgf)	LUBRICATION	BALL DIA.	20.36
MAX. ROTATIONAL SPEED (rpm)	SPACE BALL	BACKLASH	0
DN VALUE	E1 TYPE ASSEMBLY METHOD	CIRCUIT	-
MAX. FEED RATE (m/min)	CUSTOMER DRAWING NO.	LEAD ANGLE	17.36
ACCELERATION (m/sec <sup>2</sup> )	CUSTOMER MC TYPE	DYNAMIC (kgf)	-
SUPPORT METHOD	CUSTOMER AXIAL TYPE	STATIC (kgf)	-
		LEAD/PITCH	20/5

PRELOAD(kgf)	-
R.D	17.084
S.F (kgf)	-
DRAG TORQUE(kgf·m)	-
DIRECTION OF TURN	R
PC DIA.	20.36
BALL DIA.	3.175

UNCHAMFERED USE  R0.5  R1  R  
 SCALE 1: X  
 MATERIAL SH: CF53 DATE 2004.12.01  
 INT: SNCM220 DWG 孫春梅  
 THREAD BALL TRACK APPD PAUL  
 HRC 56 ~ 62 PROCESS NO. G  
 CUSTR H-CHICAGO  
 DWG.NO. A10SL9A1



\*BREAK SHARP EDGE UNLESS OTHER SPECIFIED  
 \*未破利角者以R0.5MAX  
 \* THREAD END ALLOWS ABOVE LENGTH OUT OF HARDNESS TOLERANCE

DATE	MODIFICATION	APPROVED
------	--------------	----------

\* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.

HIWIN BALLSCREWS