

1
A1237QA1



2
Released by HIWIN design group.

列印者:00018028 張家瑜 印刷時間:2019/07/23 14:06:30

3
▽ (▽▽)

機密級 More Confidential

A
B
C
D
E
F
G




NOTE:
1. CORRESPONDING SHAFT HAS A ROOT DIAMETER OF 29.124mm

PRELOAD(kgf)	~
R.D.	~
S.F. (kgf)	~
DRAG TORQUE(kgf-cm)	~
DIRECTION OF TURN	R
P.C. DIA.	32.4
BALL DIA.	3.175
BACKLASH	0.04MAX
CIRCUIT	6
LEAD ANGLE	2.81
DYNAMIC (kgf)	2980
STATIC (kgf)	8190
LEAD	5

SPEC: R32-5K6-FSCEW-E

MAX. AXIAL LOAD (kgf)		LUBRICATION		BALL DIA.	3.175
MAX. ROTATIONAL SPEED (rpm)		SPACE BALL		BACKLASH	0.04MAX
DN VALUE		E1 TYPE ASSEMBLY METHOD		CIRCUIT	6
MAX. FEED RATE (m/min)		CUSTOMER DRAWING NO.		LEAD ANGLE	2.81
ACCELERATION (m/sec ²)		CUSTOMER MC TYPE		DYNAMIC (kgf)	2980
SUPPORT METHOD		CUSTOMER AXIAL TYPE		STATIC (kgf)	8190
				LEAD	5



UNCHAMFERED USE	<input type="checkbox"/> CO.5	<input checked="" type="checkbox"/> C1	<input type="checkbox"/> C
ROUGH M/C	25a	6.3a	0.4a
FIN M/C	▽	▽	▽
GRD			
SCALE	1: X		
NORMAL TOLERANCE mm			
UP	6	30	120
TO	6	30	120
	±0.1	±0.2	±0.3
	±0.4	±0.5	±0.8
	±1.0	±1.0	±1.5
OVER	2400	2400	2400

MAT.	SH: ROLLED	DATE	2012.02.27
	NT: SNCM220/Equivalent	DWG	Jamin
THREAD BALL TRACK	CHK	Kai	
HRC	56 ~ 62	APPD	Michelle
CUSTR	HIWIN STD.		
DWG.NO.	A1237QA1		

機密級 More Confidential

2012.03.15	MOD. A	Cody
DATE	MODIFICATION	APPROVED

* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.

*BREAK SHARP EDGE UNLESS OTHER SPECIFIED.
*未畫倒角者去毛邊 (CO.2MAX)
● THREAD END ALLOWS ABOVE LENGTH OUT OF HARDNESS TOLERANCE

03:90:~ 列印者:00018028 張家瑜 印刷時間:2019/07/23 14:06:30

HIWIN BALLSCREWS