



A12EWOA2

Released by HIWIN design group.

$\nabla \nabla \nabla$  (G)

1500



TPU WIPER BOTH ENDS  
(两端附TPU刮屑环)

PRELOAD(kgf)	40
R.D.	12.539
S.F. (kgf)	0.06~0.68
DRAG TORQUE(kgf-cm)	0.11~1.31
DIRECTION OF TURN	R
P.C. DIA.	15.67
BALL DIA.	3
BACKLASH	0
CIRCUIT	3
LEAD ANGLE	11.48
DYNAMIC (kgf)	1010
STATIC (kgf)	1670
LEAD/PITCH	10/5

SPEC: 2R15-10K3- FSCEW-1500-1500-0.023

MAX. AXIAL LOAD(kgf)	LUBRICATION	BALL DIA.
MAX. ROTATIONAL SPEED (rpm)	SPACE BALL	BACKLASH
DN VALUE	E1 TYPE ASSEMBLY METHOD	CIRCUIT
MAX. FEED RATE(m/min)	CUSTOMER DRAWING NO.	LEAD ANGLE
ACCELERATION (m/sec <sup>2</sup> )	CUSTOMER MC TYPE	DYNAMIC (kgf)
SUPPORT METHOD	CUSTOMER AXIAL TYPE	STATIC (kgf)
		LEAD/PITCH

	UNCHAMFERED USE <input checked="" type="checkbox"/> C0.5 <input type="checkbox"/> C1 <input type="checkbox"/> C	SCALE	MAT.	SH: CF53/Equivalent	DATE	2013.12.20																												
	ROUGH M/C/FIN M/C/GRD	1: X	INT: SNCM220/Equivalent	DWG	Kent																													
<table border="1"> <tr><th colspan="7">NORMAL TOLERANCE mm</th></tr> <tr><td>UP</td><td>6</td><td>30</td><td>120</td><td>300</td><td>600</td><td>1200</td></tr> <tr><td>TO</td><td>±0.1</td><td>±0.2</td><td>±0.3</td><td>±0.4</td><td>±0.5</td><td>±0.8</td></tr> <tr><td>OVER</td><td></td><td></td><td></td><td></td><td>±1.0</td><td>±1.5</td></tr> </table>	NORMAL TOLERANCE mm							UP	6	30	120	300	600	1200	TO	±0.1	±0.2	±0.3	±0.4	±0.5	±0.8	OVER					±1.0	±1.5	THREAD BALL TRACK	CHK	Akuan			
NORMAL TOLERANCE mm																																		
UP	6	30	120	300	600	1200																												
TO	±0.1	±0.2	±0.3	±0.4	±0.5	±0.8																												
OVER					±1.0	±1.5																												
<table border="1"> <tr><th colspan="7">NORMAL TOLERANCE mm</th></tr> <tr><td>UP</td><td>6</td><td>30</td><td>120</td><td>300</td><td>600</td><td>1200</td></tr> <tr><td>TO</td><td>±0.1</td><td>±0.2</td><td>±0.3</td><td>±0.4</td><td>±0.5</td><td>±0.8</td></tr> <tr><td>OVER</td><td></td><td></td><td></td><td></td><td>±1.0</td><td>±1.5</td></tr> </table>	NORMAL TOLERANCE mm							UP	6	30	120	300	600	1200	TO	±0.1	±0.2	±0.3	±0.4	±0.5	±0.8	OVER					±1.0	±1.5	HRC 56 ~ 62	APPD	Kai			
NORMAL TOLERANCE mm																																		
UP	6	30	120	300	600	1200																												
TO	±0.1	±0.2	±0.3	±0.4	±0.5	±0.8																												
OVER					±1.0	±1.5																												
<table border="1"> <tr><td>1/300p:</td><td>0.023</td></tr> <tr><td>ep:</td><td>0.115</td></tr> </table>	1/300p:	0.023	ep:	0.115			CUSTR	H-CHICAGO																										
1/300p:	0.023																																	
ep:	0.115																																	
			DWG.NO.	A12EWOA2																														

\*BREAK SHARP EDGE UNLESS OTHER SPECIFIED.  
\*未量倒角者去毛邊 (CO.2MAX)  
\* THREAD END ALLOWS ABOVE LENGTH OUT OF HARDNESS TOLERANCE.

2013.12.20	MOD.	Kai
DATE	MODIFICATION	APPROVED

\* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.