



A12PJGA2

More Confidential

$\sqrt{Ra6.3}$ ($\sqrt{Ra0.4}$)



NOTE:

1. CORRESPONDING SHAFT HAS A ROOT DIAMETER OF 12.539mm


△	PRELOAD(kgf)	~
	R.D.	~
△	S.F. (kgf)	~
△	DRAG TORQUE(kgf-cm)	~
	DIRECTION OF TURN	R
	P.C. DIA.	15.67
	BALL DIA.	3
△	BACKLASH	0.04MAX
	CIRCUIT	3
	LEAD ANGLE	11.48
	DYNAMIC (kgf)	1010
	STATIC (kgf)	1670
	LEAD	10

SPEC: 2R15-10K3-FSCEW-E

MAX. AXIAL LOAD (kgf)	LUBRICATION	BALL DIA.	3
MAX. ROTATIONAL SPEED (rpm)	SPACE BALL	BACKLASH	△ 0.04MAX
DN VALUE	E1 TYPE ASSEMBLY METHOD	CIRCUIT	3
MAX. FEED RATE (m/min)	CUSTOMER DRAWING NO.	LEAD ANGLE	11.48
ACCELERATION (m/sec ²)	CUSTOMER MC TYPE	DYNAMIC (kgf)	1010
SUPPORT METHOD	CUSTOMER AXIAL TYPE	STATIC (kgf)	1670
		LEAD	10

UNCHAMFERED USE	■ C0.5	□ C1	□ C	MAT.	SH: ROLLED	DATE	2021.01.20
ROUGH M/C/FIN M/C/I	GRD	SCALE	1: X	INT: SNCM220/Equivalent	DWG	Hanna	
$\sqrt{Ra25}$	$\sqrt{Ra6.3}$	$\sqrt{Ra0.4}$		THREAD BALL TRACK	CHK	Shower	
NORMAL TOLERANCE mm				HRC 56 ~ 62	APPD	Sting	
UP TO	6	30	120	300	600	1200	2400
	±0.1	±0.2	±0.3	±0.4	±0.5	±0.8	±1.0
							±1.5
HIWIN BALLSCREWS				CUSTR	H-CHICAGO		
				DWG.NO.	A12PJGA2		

*BREAK SHARP EDGE UNLESS OTHER SPECIFIED.
*未量倒角者去毛邊 (CO.2MAX)
● THREAD END ALLOWS ABOVE LENGTH OUT OF HARDNESS TOLERANCE.



2021.01.20	MOD.	Sting
DATE	MODIFICATION	APPROVED

* PLEASE IGNORE CHINESE CHARACTERS WHICH ARE FOR OUR REFERENCE ONLY.